

ファインシール/OSC代表物性

製品	比表面積	pH (5%)	水分	篩い残分	吸油量	シリカ分	白度	平均粒子径
	m ² /g		%	%	ml/100g	%		μm
Finesil X-12	262.0	6.5	6.1	<0.05	230.0	94.3	98.3	12.3
Finesil X-35	262.0	6.6	5.8	<0.05	240.0	94.4	98.5	2.4
Finesil X-37	263.0	6.4	6.2	<0.05	230.0	94.8	98.9	3.1
Finesil X-37B	273.0	6.5	6.0	<0.05	230.0	94.6	98.1	4.2
Finesil X-30	286.0	6.5	5.8	<0.05	210.0	94.8	98.9	3.9
Finesil X-40	285.0	6.6	5.9	<0.05	220.0	95.2	99.1	2.9
Finesil X-45	291.0	6.8	6.1	<0.05	210.0	94.6	98.7	5.1
Fineseil X-60	289.0	6.7	6.0	<0.05	210.0	93.9	98.6	6.6
Finesil B	181.0	6.0	5.7	<0.05	280.0	93.7	98.5	2.9
Finesil E-50	182.0	6.1	5.8	<0.05	270.0	94.3	99.1	2.5
Finesil T-32	181.0	5.9	6.2	<0.05	280.0	94.2	99.2	2.2
Finesil US-F	189.0	6.2	6.1	<0.05	220.0	94.8	99.1	2.4
OSC C132	193.0	6.6	6.0	<0.5	220.0	>93	99.2	13.2
OSC C136	215.0	6.5	6.0	<0.5	220.0	>93	99.2	13.6
OSC C152	168.0	6.5	5.8	<0.5	220.0	>93	99.1	14.8
OSC C158	163.0	6.9	6.0	<0.5	270.0	>93	98.9	15.5
OSC 927	210.0	6.4	6.2	<0.5	230.0	>94	98.8	12.6
OSC UC116	210.0	6.6	6.3	<0.5	250.0	>93	99.0	12.5
OSC UC800	160.0	6.9	5.8		280.0	>93	99.0	80.0
OSC DT267	163.0	6.8	6.2	<0.5	260.0	>97	98.8	13.2
OSC DA95	90.0	7.0	5.7	<0.5		>96	98.9	8.9
OSC BM224	162.0	6.9	5.8	<0.5	240.0	>93	99.3	21.2
OSC BM225	168.0	6.8	5.5	<0.5	250.0	>93	99.0	20.8
OSC T610	180.0	6.8	5.2	<0.5	260.0	>93	99.1	6.5
分析方法	ISO 5794-1	ISO 787-9	ISO 787-2	ISO 3262-19	ISO 4656	ISO 5794-1	ISO 5794-1	粒度分布系